



**DESIGNED FOR USE WITH
MODEL 2 AND STH10**

- Model AR provides two signals — alert and attack
- Available in 120/240VAC power

Mechanical Siren Activating Controls

Model AR Timer

The Model AR timer provides Alert and Attack signals for the Model 2 and the Model STH10, electro-mechanical sirens. The Alert signal is a three minute steady signal, while the Attack is a three minute wail signal.

The Model AR is equipped with push buttons for activating the siren. Both signals are activated by simply pushing a button. In the event of accidental activation, a cancel button permits cancellation of a signal already in progress. A fourth test button is provided which activates the siren for only as long as it is pressed.


Two lights on the front of the timer indicate status; red indicates that the timer is in mid-cycle and amber indicates that power is available to the timer.

A Model AR Timer is the activating control for Models 2 and STH10 electro-mechanical sirens.

Model	Voltage	Signals	Signal Time
AR	120/240VAC	Steady and Wail	3 minutes



ACTIVATING CONTROLS (AR)



SPECIFICATIONS

Net Weight:	10.9 lbs.	4.94 kg
Shipping Weight:	11 lbs.	4.99 kg
Height:	10.0"	254 mm
Depth:	4.0"	101.6 mm
Width:	8.0"	203.2 mm

HOW TO ORDER

- Specify model and voltage
- *Call the factory for assistance in specifying an outdoor warning system*